



ЕВРАЗИЙСКИЙ ЭКОНОМИЧЕСКИЙ СОЮЗ ДЕКЛАРАЦИЯ О СООТВЕТСТВИИ



Заявитель ОБЩЕСТВО С ОГРАНИЧЕННОЙ ОТВЕТСТВЕННОСТЬЮ "НАБЛЮДАТЕЛЬНЫЕ ПРИБОРЫ"

Место нахождения (адрес юридического лица) и адрес места осуществления деятельности: 194021, Россия, г. Санкт-Петербург, вн.тер.г. Муниципальный округ Пискаревка, ул. Новороссийская, д. 53, литера Б, помещ. 74.

Основной государственный регистрационный номер 1079847102829.

Телефон: +79055325811 Адрес электронной почты: info@nr.ru

в лице Генерального директора Наумова Константина Витольдовича

заявляет, что Оборудование осветительное не бытового назначения: светодиодное, люминесцентное и работающее с лампами накаливания, лампами-вспышками, в том числе в комплектах: осветители, панели, светильники, прожекторы и лампы узконаправленного света, осветительные блоки и патроны (светильники), Торговая марка: «Falcon Eyes», «GreenBean», «Veber», «Микромед», согласно приложению № 1 на 4 листах.

Изготовитель "Wenzhou Changcheng Photo-Facility Co., Ltd"

Место нахождения (адрес юридического лица) и адрес места осуществления деятельности по изготовлению продукции: Китай, № 5 Jucheng Road, Juguang Garden, Wenzhou Hi-tech Zone, 325000 Wenzhou

Код (коды) ТН ВЭД ЕАЭС: 9405

Серийный выпуск

соответствует требованиям

Технического регламента Таможенного союза "О безопасности низковольтного оборудования" (ТР ТС 004/2011)

Технического регламента Таможенного союза "Электромагнитная совместимость технических средств" (ТР ТС 020/2011)

Декларация о соответствии принята на основании

Протокола испытаний № МПС/ПСР-3484 от 27.06.2023 года, выданного Испытательной лабораторией Общества с ограниченной ответственностью «МАШПРОМСЕРТ» (регистрационный номер аттестата аккредитации РОСС RU.32055.ИЛ.00007)

Схема декларирования соответствия: 1д

Дополнительная информация

ГОСТ 12.2.007.0-75 "Система стандартов безопасности труда. Изделия электротехнические. Общие требования безопасности", ГОСТ 30804.6.2-2013 (IEC 61000-6-2:2005) "Совместимость технических средств электромагнитная. Устойчивость к электромагнитным помехам технических средств, применяемых в промышленных зонах. Требования и методы испытаний", СТБ IEC 61000-6-4-2012 "Электромагнитная совместимость. Часть 6-4. Общие стандарты. Помехоэмиссия от оборудования, предназначенного для установки в промышленных зонах" раздел 7. Дата изготовления, срок годности, условия хранения указаны в прилагаемой к продукции товаросопроводительной документации и/или на упаковке и/или каждой единице продукции. Декларация соответствия распространяется на продукцию, изготовленную с даты изготовления отобранных образцов (проб) продукции, прошедших исследования (испытания) и измерения: 01.01.2020 года. Договор уполномоченного лица № 1 от 14.01.2019 года.

Декларация о соответствии действительна с даты регистрации по 27.06.2024 включительно.

(подпись)

М.П. «Наблюдательные приборы»
ОБЩЕСТВО С ОГРАНИЧЕННОЙ ОТВЕТСТВЕННОСТЬЮ
194021, РОССИЯ, Г. САНКТ-ПЕТЕРБУРГ, УЛ. НОВОРОССИЙСКАЯ, Д. 53, ЛИТЕРА Б, ПОМЕЩ. 74
ИНН 78-07-0000000000
ОГРН 1079847102829
САНКТ-ПЕТЕРБУРГ

Наумов Константин Витольдович

(Ф.И.О. заявителя)

Регистрационный номер декларации о соответствии: ЕАЭС N RU Д-CN.РА05.В.00156/23

Дата регистрации декларации о соответствии: 28.06.2023

ЕВРАЗИЙСКИЙ ЭКОНОМИЧЕСКИЙ СОЮЗ

ПРИЛОЖЕНИЕ №1 Лист 1

к ДЕКЛАРАЦИИ О СООТВЕТСТВИИ ЕАЭС N RU Д-СН.РА05.В.00156/23
Перечень продукции, на которую распространяется действие декларации о соответствии

Код (коды) ТН ВЭД ЕАЭС	Наименование, типы, марки, модели продукции, составные части изделия или комплекса
	<p>RFL 10W-1, LFPB-2 kit, HL-150, RFL-10W, PBK-50AB-2LS, PBK-50AB-3LED, RFL10W, RFL10W-1, Dual Goose LED, DFL-C554, DFL-C556, DFL-C552, FLC-22, FLC-28, FLC-40, DFL-C102, DFL-C104, DFL-C106, 6240, 3220, 4730, RFL, LFPB-1 kit, LFPB-2 kit, LFPB-3 kit, LFPB-4 kit, PBK-1 kit, PBK-2 kit, PBK-3 kit, PBK-4 kit, FLB-616AB, FLB-416AB, SoftLight 455, SoftLight 255, SoftLight 655, DS-1000, DS-500, DTR-800, DTR-800A, DTR-800A+RHS800, DTR-2000, QL-1000, QL-1000 BW, QL-1000 BWGY9.5, QL-1000 BWGY9.5, QL-1000 BW GX9.5, QL-500, QL-500BW, QL-500BW GY9.5, QL-500BW, GX9.5, QL-32, QL-45, QL-50, QL-66, QL-88, QL-75, QL-75B, QL-75D, QL-100, QL-120, QL-100B, QL-100D, QL-200, QL-250, QL-250T, QL-250D, LHD-500, LHD-500BW, NL-2000, NL-250, NL-300, NL-500, HL-30, HL-50, HL-1, HL-2, HL-150, HL-250, HL-500, QLBK-500, QLBK-1000, EXFK-6080, LHPAT-15-1, LHPAT-32-3, LHPAT-40-1, LHPAT-21-1, LHPAT-26-1, LHD-40-5, LHD-40-4, FLC-22, FLC-40, LHD-3250Q, LHD-5250Q, LHP-328Q, LHD-3250, LHD-5250, LHP-328, Fresnel 100, Fresnel 200, Fresnel 300, Fresnel 400, Fresnel 500, Fresnel 600, Fresnel 650, Fresnel 1000, Fresnel 2000, Fresnel 3000, Fresnel 4000, Fresnel 10, Fresnel 20, Fresnel 30, QL-250T A, QL-250T B, QL-250T C, QL-250D A, QL-250D B, QL-250D C, QL-250D B, QL-250T, QL-250D, ProStudio, ProStudio 01, ProStudio 02, ProStudio 03, ProStudio 04, ProStudio 07, QLK-220 Kit, QLK 2-150/1-200 Kit, QLK-3-150 Kit, QLK-2150 Kit, RedLight 650, RedLight 650D, DTR-800D, DTR-kit V-Light 60 LED BW, LPS-60LED BW, V-Light 100LED BW, LPS-100LED BW, V-Light 80 LED BW, LPS-80LED BW, LG-500, LG-900, DV-60K, LG-500/LED, LG-900/LED, LE-500/LED, LQ-500, LQ-500/LED, LC-500/LED, LE-100/LED, DMAF48 LED, DMAF10 LED, LED-1, LED-2, LED-V80, LED-V300, LED-V100, LED-126, LED-140, LED-228, LED-48, LED-48T, LED-48H, LED-64, LED-64T, LED-70, LED, LED-240BC, LED-240CH, LED-228H, LG-500 B/LED, LG-900 B/LED, LED-300A, LEP-600A, 300LED, 600LED, 900LED, 1200LED, DVR-240D-2, SLPK-2120LTV, LP-DB820CT-SY, DV-3B, LP-D1603F, DVR-240DF, LP-DB2005CT-SY, DV-96V-K1, DV-216VC-K2, DV-384CT-K3, LED-160, LED-198, LG-1400 LED, LG-2800 LED, LG-1600 LED, LP-1400 LED, LP-2800 LED, LP-1600 LED, QL-100 PRO, GB-300LED, GB-600LED, GB-800LED, GB-500LED, GB-900LED, iLed, iLed-10, GB-1200, GB-LED1000, GB-LED500, GB-LED10, GB-LED30, GB-LED1400, GB-LED2800, GB-LED 1600, GB-5LED, GB-10LED, GB-5B LED, GB miniLED, miniLED 08, DayLight 150 LED, Hi-light 100, Hi-light 200, Hi-light 300, Hi-light 400, Hi-light 500, Hi-light 600, Hi-light 700, Hi-light 800, Hi-light 900, Hi-light 1000, Hi-light 1200, Hi-light 1400, Hi-light 2800, Fresnel 100 Led, Fresnel 150 Led, Fresnel 180 Led, Fresnel 200 Led, Fresnel 250 Led, Fresnel 300 Led, Fresnel 1000 LED, Fresnel 400 LED, Fresnel 500 LED, Fresnel 10 LED, Fresnel 30 LED, Fresnel 20 LED, Fresnel 1500 LED, Fresnel 2000 LED, Sunlight 500, Sunlight 1000, Sunlight 800, Sunlight 10, Sunlight 20, Sunlight 30, Sunlight 2000, Sunlight 1500, Sunlight 1200, GB LED-332, iLED-32, LED BOX 98, LED BOX 209, LED BOX 312, LED BOX 144, LED BOX 500, LED BOX 600, LED BOX 700, LED BOX 800, LED BOX 900, LED BOX 1000, LED BOX 1100, LED BOX 1200, LED BOX 1300, LED BOX 1400, LED BOX 98B, LED BOX 209B, LED BOX 312B, LED BOX 144B, LED BOX 500B, LED BOX 600B, LED BOX 700B, LED BOX 800B, LED BOX 900B, LED BOX 1000B, LED BOX 1100B, LED BOX 1200B, LED BOX 1300B, LED BOX 1400B, DayLight 160 LED, DayLight 170 LED, DayLight 180 LED, DayLight 190 LED, DayLight 200 LED, DayLight 300 LED, DayLight 500 LED, DayLight 600 LED, DayLight 900 LED, DayLight 150 V-Mount, DayLight 150 LED V-Mount, iLed studio 01, iLed studio 02, iLed studio 03, LED studio 01, LED studio, LED studio 02, LED studio 03, broadcasting studio, broadcasting studio 01, broadcasting studio 02, broadcasting studio 03, Zoom 6 LED, Zoom 5 LED, Zoom 4 LED, Zoom 3 LED, ZOOM 2 LED, Zoom 1 LED, Panel 900LED, Panel 1300LED, BL-500P, BL-600P, BL-900P, BL-900PB, BL-1300P, BL-1300PB, LED BOX 600Bi, LED BOX 900Bi, LED BOX 1300Bi, LP-D40, LP-D40R, LP-D60, LP-D60R, LP-D80, LP-D80R, LP-500, LP-500U, LP-1000, LP-1000U, LP-D500, LP-D1000, LPK-2500U, LP-DB1000-SY, LP-DB1000-AB, LP-D1603F, LP-DB820-SY, LP-DB820-AB, LP-DB820CT-SY, LP-DB820CT-AB, LP-1600, LP-DB800-SY, LP-DB800-AB, LP-1400, LP-2800, DV-112V, DV-112LTV, DV-112V-K, DV-112LTV-K, DV-126DB, DV-126DB-K, DV-126V-K, DV-256V, DV-320VC, SLP-120LTV, SLP-200V, SP-AC15V-02, SLPK-2120LTV, SLPK-2200V, VL-60V, DV-3A, DV-3B, UltraPanel 576 LED, UltraPanel 1806 LED, UltraPanel 1092 LED, LG-500 LED v-mount, LG-900 LED v-mount, LG-500 B/LED v-mount, LG-500B/LED v-mount, LG-900 B/LED v-mount, LG-900B/LED v-mount, LedRing 50, LedLine 516, LedLine 516B, GB</p>



Генеральный директор

(Handwritten signature)
подпись

Наумов Константин Витольдович
(Ф.И.О. заявителя)

ЕВРАЗИЙСКИЙ ЭКОНОМИЧЕСКИЙ СОЮЗ

ПРИЛОЖЕНИЕ №1 Лист 2

к ДЕКЛАРАЦИИ О СООТВЕТСТВИИ ЕАЭС N RU Д-СН.РА05.В.00156/23

Перечень продукции, на которую распространяется действие декларации о соответствии

Код (коды) ТН ВЭД ЕАЭС	Наименование, типы, марки, модели продукции, составные части изделия или комплекса
	<p>LED 332, SunLight 200 LED BW, SunLight 100 LED BW, SunLight 250 LED BW, SunLight 300 LED BW, DayLight 150 LED v-mount, Fresnel 100 LED X3 DMX, Fresnel 150 LED X3 DMX, Fresnel 200 LED X3 DMX, Fresnel 300 LED X3 DMX, Fresnel 100 LED X3, Fresnel 150 LED X3, Fresnel 200 LED X3, Fresnel 300 LED X3, LedLine 360B, LedLine 720B, DayLight 42 Led, DayLight 60 LED, DayLight 42B Led, DayLight 60B LED, LuxMan 128 LED, LuxMan 256 LED, LuxMan 312 LED, LuxMan 128B LED, LuxMan 256B LED, LuxMan 312B LED, Vivi-2500S, 45W LED, Bi-color LEDLight, KeyLight 40 LED, KeyLight 50 LED, KeyLight 60 LED, KeyLight 80 LED, KeyLight 100 LED, Fresnel 100 Led X2, Fresnel 150 Led X2, Fresnel 180 Led X2, Fresnel 200 Led X2, UltraPanel 576 LED bd, UI, StudioLED 75 BW, StudioLED KIT 275-SB, StudioLED, LedPRO 64, LedPRO 126, LedPRO 170, LedPRO 308, LedPRO 308 bi color, LedPRO, LED-56, LED-60, Goose Led, LED-MC-3, LED-MC-4, LED-MC-5, UltraPanel 576 LED BD, UltraPanel 1806 LED BD, UltraPanel 1092 LED BD, StudioLED 200 BW, StudioLED 150 BW, StudioLED 100 BW, StudioLED 60 BW, StudioLED KIT 260-SB, miniLight VL-45 LED, miniLight 45 LED, miniLight 245LED U-KIT, miniLight VL-35 LED, miniLight 35 LED, miniLight 235LED U-KIT, KeyLight 518 SB5070, KeyLight 518 SB-KIT, KeyLight 918 OCT90, KeyLight 918 OCT-KIT, DTR-60LED, DTR-45LED, DTR-80LED, DTR-100LED, DayLight 80 LED Bi-Color, DayLight 100 LED Bi-Color, DayLight 200 LED Bi-Color, DayLight 80B LED Studio, DayLight 100B LED Studio, DayLight 200B LED Studio, LedCube 30, LedCube 40, LedCube 50, LedCube 60, Fresnel 300M LED DMX, Fresnel 200BM LED DMX bi-color, SunLight 200 LEDX2 BW, SunLight 100 LEDX2 BW, Fresnel 100 LEDX3 DMX, Fresnel 150 LEDX3 DMX, Fresnel 200 LEDX3 DMX, Fresnel 300 LEDX3 DMX, Fresnel 500 LED X3 DMX, Fresnel 500 LED X3 Bi-color DMX, LedLine 360 Bi-Color, AQUALed 200, AQUALed 100, AQUALed 150, LH-27, LH-27SU, LH2-27SU, LH-27SU-H01, LH-27SU-H02, LH-27S, LHD-500, LHD-500BW, DVR-240D, DayLight 100LED DMX, DayLight 200LED DMX, LedLine 360 LCD, LedLine 360B LCD, KeyLight 518 SB5070 LED, KeyLight 125 SB5050 LED, KeyLight 425 SB6080 LED, KeyLight 525 SB50120 LED, RingLight 100 LED, RingLight 40 LED, RingLight 50 LED, RingLight 60 LED, RingLight 70 LED, RingLight 80 LED, RingLight 90 LED, LG2 900/LED NP-mount, LG2 600/LED V-mount, LG2 1100/LED V-mount, LG2 900 B/LED V-mount, LG2 600 B/LED NP-mount, LG2 1100 B/LED V-mount, LED panel 600 NP-mount, LED panel 900 V-mount, LED panel 1100 V-mount, LED panel 600B NP-mount, LED panel 900B V-mount, LED panel 1100B V-mount, FlexLight 256 LED, FlexLight 448 LED, Macro Cube 25 LED, Macro Cube 40 LED, Light Cube 40 LED, Light Cube 60 LED, Macro Studio 60 LED, SuperPoint 40 LED, SuperPoint 50 LED, SuperPoint 60 LED, SuperPoint 70 LED, SuperPoint 80 LED, SuperDot 40 LED, SuperDot 50 LED, SuperDot 60 LED, SuperDot 70 LED, SuperDot 80 LED, Zoom 40 LED, Zoom 50 LED, Zoom 60 LED, Zoom 70 LED, Zoom 80 LED, miniLight 45 LED, miniLight 245-kit LED, 1092 LED BD Bi-color, 1806 LED BD Bi-color, 576 LED BD Bi-color, LG 500 B/LED V-mount, LG 500/LED V-mount, FlatLight 600 LED, FlatLight 600 LED Bi-color, FlatLight 900 LED, FlatLight 900 LED Bi-color, FlatLight 100 LED Bi-color, FlatLight 150 LED Bi-color, ZOOM 90BW LED, ZOOM 60 LED, DayLight 100 MultiColor, DayLight 200 MultiColor, DayLight 100 Bi-Color, DayLight 200 Bi-Color, PBK-50AB-3LED, DTR-60 LED, LE-900 LED, LE-576 LED, StripLight 60 LED, BeautyLight 480 LED, BeautyLight 480RC LED, Studio LED 75, KeyLight 130 SB5050 LED, Sunlight 100 LEDX3 BW, Sunlight 200 LEDX3 BW, Studio LED 275-kit, DTR-60 LED Bi-color, LEDline 516B, FreeLight 288 bi-color, LED-36, LED-72, LED-72, LED-114, Flat LED-36, Flat LED-72, Flat LED-114, Ultranel 576 LED BD, Ultranel 576 LED BD Bi-color, Ultranel 1092 LED BD, Ultranel 1092 LED BD Bi-color, Ultranel 1806 LED BD, Ultranel 1806 LED BD Bi-color, DFL-C102, DFL-C104, DFL-C106, 6240, 3220, 4730, QLK-2150 Kit, RedLight 650, DEK-2300POP, DEK-2316POP, DEK-2300POP(M), EXFK-6080, LFPB-1 kit, LFPB-2 kit, LFPB-3 kit, VK-32, SSK-2150POP, DTR-kit, DTR-800A+RHS800, PBK, DEK, SSK, MDK, EXFK, LFPB, VK, SSKIT, DTR, HL-150, HL, DTR-2000, DTR-800, QL-50A, QL-60A, QL-70A, QL-75A, QL-100A, QL-120A, QL-150A, QL-250A, QLK-2300POP, QLK-2316POP, QLK-2300POP(M), QLBK-1000GY9.5, QLBK-500 GY9.5, QLBK-1000GX9.5, QLBK-500 GX9.5, QL-500, QL-500BW, QL-500BW Gy9.5, QL-500BW Gx9.5, QL-1000, QL-1000BW, QL-1000BW Gy9.5, QL-1000BW Gx9.5, QL-1, QL-2, QL-3, QL-4, QL-5, QL-100PRO, QL-120PRO, QL-50PRO, QL-75PRO, RedLight 650, RedLight 650B, Red Studio 01, Red Studio 02, Red Studio 03, QL-10, QL-20, QL-50, QL-55, QL-60, QL-65, QL-70, QL-75, QL-100, QL-120, QL-150, QL-250, QL-50PRO, QL-60PRO, QL-75PRO, QL</p>



Генеральный директор

(Handwritten signature)

подпись

Наумов Константин Витольдович

(Ф.И.О. заявителя)

ЕВРАЗИЙСКИЙ ЭКОНОМИЧЕСКИЙ СОЮЗ

ПРИЛОЖЕНИЕ №1 Лист 3

к ДЕКЛАРАЦИИ О СООТВЕТСТВИИ ЕАЭС N RU Д-СН.РА05.В.00156/23

Перечень продукции, на которую распространяется действие декларации о соответствии

Код (коды) ТН ВЭД ЕАЭС	Наименование, типы, марки, модели продукции, составные части изделия или комплекса
	<p>-100PRO, QL-120PRO, QL-250PRO, QLK-2100, QLK-2120, QL, MDK-250, MDK-250BG, MDK-250BG-2, MDK-250BG-3, QLK-250BG, QLK-250BG-2, QLK-250BG-3, SLK-2400S, SLK-2400U, QLK-2400S, LHD-500, LHD-500BW, QL-300, QL-400, QL-15, QL-30, QL-40, SSKIT I, SSKIT II, SSKIT LLL, SSKIT IV, SSK 2-150/1-200F PRO, QLKIT I, QLKIT II, QLKIT III, QLKIT IV, QLK 2-150/1-200F PRO, PBK-50AB-2LS, MF-32, MF-45, QF-32, SS-100, SS-120, QL-45, QLK-2-150/1-300S, QLK-2150S, SLK-2-150/1-300S, SLK-2150S, CS-730, CS-830, CS-630, CS-530, MDK-248MU, MDK-348MU, MDK-448MU, QLK-248MU, QLK-348MU, QLK-448MU, MDK-2100SS, MDK-2120SS, MDK-3120SS, QLK-150, QLK-2150 Sprinter, QLK-150 Sprinter, QLK-250 Sprinter, QL-150 Sprinter, SSK 2-150BJ/1-200BJ, SSK-2150, SSK-2150POP, SLK-2400S, RFL10W, Studio LED275-kit, miniLight 245-kit LED, LED-144T, SSK 2-150BJ/1-200BJ PRO, SSK-2150POP, UltraPanel II 576 LED BD Bi-color, UltraPanel II 576 LED, UltraPanel II 1092 LED, UltraPanel II 1092 LED Bi-color, UltraPanel II 1806 LED K, UltraPanel II 1806 LED Bi-color, UltraPanel II 2304 LED, UltraPanel II 2304 LED Bi-color, LE-576 LED, LE-576 LED RGBW, FreeLight 288 bi-color, FreeLight 336 bi-color, FreeLight 504 bi-color, DayLight II 100 LED Bi-color, DayLight II 100 LED RGB, DayLight II 200 LED Bi-color, DayLight II 200 LED RGB, MoonLight 120 LED bi-color, MoonLight 400 LED bi-color, SunLight PRO 400 LED, SunLight PRO 240 LED bi-color, SunLight PRO 240 LED Bi-color, SunLight PRO 340 LED, SunLight PRO 340 LED Bi-color, DTR-60 LED Bi-color, KeyLight 2150 SB5070, KeyLight 845 SB5070, KeyLight 3150 SB5070, KeyLight 4150 SBU, LFPB-3 kit, BeautyLight 480G LED, BeautyLight 128 LED, BeautyLight 240 LED, DTR-30 RGB LED, LH-E27x1, LH-E27x4, LH-E27x2, LH-E27x3, LH-4150, LH-E27, Studio LED 100BW, SpotLight 40LED BW, SpotLight 60LED BW, SpotLight 70LED BW, UltraPanel II 576 LED Bi-color, LP-384 LED Bi-color, SunLight 200 LEDX3 BW, SmartLED 8, DTR-60 LED Y, DTR-60 LED, BloggerKit, BloggerKit 40, BloggerKit 60, BloggerKit 100, BloggerKit 150, SmartLED 152 RGB, SunLight 100 LEDX3 BW, FreeLight 336 RGB, FreeLight 336 BW, Studio LED COB75 BW, Studio LED COB120 BW, Studio LED COB180 BW, Studio LED COB275 kit, Studio LED COB275-kit, LedPRO 168BD Bi-color, LedPRO 348BD Bi-color, SunLight PRO 300COB DMX, SunLight PRO 200COB DMX, SunLight PRO 100COB DMX, QLBK-1000 v2.0k, QLBK-500 v2.0, QL-1000BW v2.0, QL-500BW v2.0, THL-500-2, THL-1000-2, SSK 2150/1200BJM, KeyLight 225LED SB5070 KIT, KeyLight 325LED SB5070 KIT, KeyLight 425LED SBU KIT, KeyLight 825LED SB5070 KIT, QLBK-1000 v2.0, SSK 2150-1200 BJM, KeyLight 145 SB5050, KeyLight 145 SB5050 KIT, BeautyLight 128B LED, StudioLight 100 LED DMX, StudioLight 300 LED DMX, FlexLight 240 LED Bi-color, FlexLight 480 LED Bi-color, FlexLight 720 LED Bi-color, LedFlow 2ft Bi-color DMX, LedFlow 4ft Bi-color DMX, LedFlow 2ft RGB, LedFlow 4ft RGB, LedFlow 4x4ft DMX, LedFlow 2x4ft DMX, LedFlow 4x2ft DMX, LedFlow 2ft RGB (BP), LedFlow 4ft RGB (BP), KeyLight 245LED SB-BG KIT, LFPB-3 LED KIT, LHPAT-15-1c, LHPAT-15-1, LH-E27x5, StripLight 80 LED, KeyLight 518LED SB5070 KIT, KeyLight 425LED SB6080 KIT, KeyLight 425LED SB6090, KeyLight 425LED SB6090 KIT, KeyLight 418LED SB5070 KIT, KeyLight 4150 SBU KIT, Flat LED 40, Flat LED 60, Flat LED 80, Flat LED 120, StripLight 90 LED, StripLight 200 LED Bi-color, DayLight III 60 LED Bi-color, DayLight III 90 LED Bi-color, DayLight III 120 LED Bi-color, DayLight III 300 LED Bi-color, DayLight III 400 LED Bi-color, DayLight III 500 LED Bi-color, DayLight III 600 LED Bi-color, DayLight III 60 LED RGB, DayLight III 90 LED RGB, DayLight III 120 LED RGB, DayLight III 300 LED RGB, DayLight III 400 LED RGB, LedPRO 308 bi-color, LedPRO 308 Bi-color, BloggerKit 20 mic, LEDFly 5 Bi-color, LedPRO 416 Bi-color, ZOOM 120BW LED, DayLight III 100 LED Bi-color, DayLight III 200 LED Bi-color, LedFlow 4x2ft DMX (GH), LedFlow 4x4ft DMX (GH), Fresnel 200 LED X3 Bi-color DMX, Fresnel 300 LED X3 Bi-color DMX, Phantom 800 HSS, Phantom 600 HSS, Phantom 400 HSS, LedPRO-M 15 Bi-color, LedPRO-M 30 Bi-color, Studio LED COB 80 BP, Studio LED COB 120 BP, BeautyLight 480LS LED, V-LED 64 RGB, V-LED 120 RGB, StudioLight II 200 bi-color, StudioLight II 200, StudioLight II 100 bi-color, StudioLight II 100, SmartLED T88 RGB, StudioLight II 300 bi-color, StudioLight II 300, LE-120PRO RGB DMX, SmartLED 196 RGB, SmartLED R66 RGB, SmartLED X158 RGB, Fresnel 200 RGB X3 DMX, FreeLight 672 bi-color, SunLight PRO 500 LED, BeautyLight 450R LED, Studio LED 200 Bi-color, Space 600B, Space 600D, SSK-2120 U-KIT, BloggerKit 07 mic, LED 200D BW, KeyLight II 3200D SBL KIT, LED 150B BW, KeyLight II 2150B SB KIT, LE-576A RGBW, Studio LED 100RGB, LH-</p>

Генеральный директор



подпись

Наумов Константин Витольдович

(Ф.И.О. заявителя)

ЕВРАЗИЙСКИЙ ЭКОНОМИЧЕСКИЙ СОЮЗ

ПРИЛОЖЕНИЕ №1 Лист 4


к ДЕКЛАРАЦИИ О СООТВЕТСТВИИ ЕАЭС N RU Д-СН.РА05.В.00156/23

Перечень продукции, на которую распространяется действие декларации о соответствии

Код (коды) ТН ВЭД ЕАЭС	Наименование, типы, марки, модели продукции, составные части изделия или комплекса
	27x1, LedFlow 4ft RGB DMX, LedFlow 2ft RGB(BP), StripLight 264 RGB, PBK-50AB-2LED, PBK-50AB-3LED, DayLight PRO 600RGB, PB-210D, PB-210B, LedFlow 2ft RGB DMX, Cell 80D, Cell 80B, Cell 80RGB, 440 SB6080 KIT, KeyLight 440 SB6080 KIT, KeyLight 440 LED SB6080 KIT, SpaceLight 4H Bi, SpaceLight 4H RGB, SpaceLight 9H Bi, Copy Stand 107, LE-576R, LE-576RX, Dual Goose 150 Fiber, KeyLight III 2150D SB KIT, KeyLight III 2200D SB KIT, TL-120RGB, TL-60RGB, TL-30RGB, TL-20RGB



Генеральный директор



подпись

Наумов Константин Витольдович

(Ф.И.О. заявителя)